

WINTECH



ACCESS DOORS

Test Port Guidelines

WinTech uses the VentLok 699 Test Port and gasket in all of our current door systems.



Test ports are attached and sealed with two (2) rivets and VentLok Gasket to outside of door skin. Test ports consist of 6063-T5 aluminum tubing with an I.D. (Inside Diameter) of 1". Test port tube is sealed to inside face of door skin with Polyurethane UV stable sealant



All test ports are located at center of door in width and height. In the event a view port and test port are required, test ports will be located at 4" below view port cut out and centered in the width of door. If special / custom test port location is needed, notification must be given at time of purchase order.

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION INTENDED FOR THE PRIVATE USE OF WINTECH AND ITS CUSTOMERS. ©2010 Window Technology, Inc. (dba WinTech) ALL RIGHTS RESERVED